

TECHNICAL SHEET

TSP 930 – Finixa control spray

Product information

The temporary gloss layer of the Finixa Control spray replaces the clear coat without leaving any trace on the surface. TSP 930 is the perfect tool to detect imperfections.

The gloss layer works as a magnifying glass and it will detect errors faster and easier.

Finixa control spray evaporates completely after use without leaving any residue on the sprayed surface (+/- 10-15min. at 20°C and normal humidity).

Instructions

Color control:

Spray a thin layer of Finixa control spray on a sample plate that is sprayed with a basecoat to create a temporary shine. Compare the sample plate with the desired color for inspection.

Abrasion cracks and imperfections:

Spray a thin layer of Finixa control spray on the treated surface, the gloss layer will act as a magnifying glass, making all possible imperfections more visible. As a result, sanding scratches (most of the time it will be visible after spraying a clear coat) will be detected early.

Let the Finixa control spray evaporate or accelerate by using a wide blow gun (WJE 05).

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for his application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Chemicar Europe cannot be held responsible for product failure unless full testing has been carried out. The client has to decide on the product's suitability for their own applications.